

Tastschalter 10 AX 250 V~ mit Abdeckung und Wippe 2fach Serienschalter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0125 40	1/5	31,03	01	4010337125402
 Grau	0125 42	1/5	31,03	11	4010337125426
 Rot	0125 43	1/5	31,03	11	4010337125433
 Blau	0125 46	1/5	31,03	11	4010337125464
 Schwarz	0125 47	1/5	31,03	11	4010337125471

Technische Daten

Einbautiefe	
- 0125 ...:	28 mm
- 0128 ...:	32 mm
Anschlussquerschnitt	
- für starre und flexible Leiter bis:	2,5 mm ²
Nennleistung	
- LEDi/ CFLi:	100 W