

Tastschalter 10 AX 250 V~ mit Abdeckung und Wippe Kreuzschalter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0127 40	1/5	31,08	01	4010337127406
 Grau	0127 42	1/5	31,08	11	4010337127420
 Rot	0127 43	1/5	31,08	11	4010337127437
 Blau	0127 46	1/5	31,08	11	4010337127468
 Schwarz	0127 47	1/5	31,08	11	4010337127475

Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm ²
Nennleistung - LEDi/ CFLi:	100 W

Hinweise

- Soll dieser Schalter beleuchtet werden, bitte Kontrollschalter vorsehen.