

Lautsprecher Unterputz-Radio



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|----|--------------------|----|---------------|
|  Cremeweiß glänzend | 2282 01 | 1 | 26,73 | 03 | 4010337076230 |
|  Reinweiß glänzend | 2282 03 | 1 | 26,73 | 03 | 4010337076247 |
|  Reinweiß seidenmatt | 2282 27 | 1 | 26,73 | 03 | 4010337076254 |
|  Anthrazit | 2282 28 | 1 | 28,78 | 03 | 4010337076261 |
|  Farbe Alu | 2282 26 | 1 | 31,35 | 03 | 4010337076162 |
|  Schwarz matt | 2282 005 | 1 | 31,35 | 03 | 4010337037286 |
|  Grau matt | 2282 015 | 1 | 31,35 | 03 | 4010337083931 |
|  Edelstahl | 2282 600 | 1 | 35,98 | 03 | 4010337032861 |

Merkmale

- Lautsprecher zum Anschluss an das Gira Unterputz-Radio.

Technische Daten

Einbautiefe: 32 mm

Anschlussquerschnitt
- Lautsprecher-/AUX-Anschluss: 1,5 mm²

Impedanz: 8 Ω

Umgebungstemperatur: -5 °C bis +50 °C
