

**Tastschalter 10 AX 250 V~ mit gerade stehender Wippe 2fach
Wechselschalter 2fach**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß glänzend	2861 201	1/5	40,02	01	4010337065883
 Reinweiß seidenmatt	2861 27	1/5	40,02	01	4010337053286
 Anthrazit	2861 28	1/5	40,54	11	4010337053293
 Farbe Alu	2861 26	1/5	43,74	11	4010337053279
 Edelstahl	2861 600	1/5	50,74	11	4010337021209

Technische Daten

Einbautiefe	
- 2860 ...	28 mm
- 2861 ...	32 mm
Anschlussquerschnitt	
- für starre und flexible Leiter bis:	2,5 mm ²
Nennleistung	
- LEDi/ CFLi:	100 W