

**Tastschalter 10 AX 250 V~ mit Abdeckung und Wippe 2fach  
Wechselschalter 2fach**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0128 40	1/5	41,65	01	4010337128403
 Grau	0128 42	1/5	41,65	11	4010337128427
 Rot	0128 43	1/5	41,65	11	4010337128434
 Blau	0128 46	1/5	41,65	11	4010337128465
 Schwarz	0128 47	1/5	41,65	11	4010337128472

**Technische Daten**

Einbautiefe	
- 0125 ...:	28 mm
- 0128 ...:	32 mm
Anschlussquerschnitt	
- für starre und flexible Leiter bis:	2,5 mm <sup>2</sup>
Nennleistung	
- LEDi/ CFLi:	100 W