

**Tastschalter 10 AX 250 V~ mit Abdeckung und Wippe 2fach  
Wechselschalter 2fach**



| Spezifikation                                                                               | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---------------------------------------------------------------------------------------------|-------------|-----|--------------------|----|---------------|
|  Reinweiß | 0128 40     | 1/5 | 41,65              | 01 | 4010337128403 |
|  Grau    | 0128 42     | 1/5 | 41,65              | 11 | 4010337128427 |
|  Rot     | 0128 43     | 1/5 | 41,65              | 11 | 4010337128434 |
|  Blau    | 0128 46     | 1/5 | 41,65              | 11 | 4010337128465 |
|  Schwarz | 0128 47     | 1/5 | 41,65              | 11 | 4010337128472 |

**Technische Daten**

|                                       |                     |
|---------------------------------------|---------------------|
| Einbautiefe                           |                     |
| - 0125 ...                            | 28 mm               |
| - 0128 ...                            | 32 mm               |
| Anschlussquerschnitt                  |                     |
| - für starre und flexible Leiter bis: | 2,5 mm <sup>2</sup> |
| Nennleistung                          |                     |
| - LEDi/ CFLi:                         | 100 W               |