

**Taster 10 A 250 V~ mit gerade stehender Wippe
Wechsler 1-polig**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß glänzend	0130 201	1/5	19,18	01	4010337066064
 Reinweiß seidenmatt	0130 27	1/5	19,18	01	4010337029434
 Anthrazit	0130 28	1/5	19,91	11	4010337029458
 Farbe Alu	0130 26	1/5	23,08	11	4010337029441
 Schwarz matt	0130 005	1/5	23,08	11	4010337037910
 Grau matt	0130 015	1/5	23,08	11	4010337077183
 Edelstahl	0130 600	1/5	29,95	11	4010337035947

Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm ²