

SCHUKO-Steckdose 16 A 250 V~ mit Shutter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0453 40	1/5	15,62	01	4010337453406
 Grau	0453 42	1/5	15,62	11	4010337453420
 Rot	0453 43	1/5	15,62	11	4010337453437
 Grün	0453 45	1	15,62	11	4010337453451
 Blau	0453 46	1/5	15,62	11	4010337453468
 Schwarz	0453 47	1/5	15,62	11	4010337453475

Technische Daten

Einbautiefe:	31 mm
Anschlussquerschnitt - für Leiter von:	1,5 mm² bis 2,5 mm²
Umgebungstemperatur - Shutter:	0 °C bis 45 °C

Hinweise

- Erhöhter Berührungsschutz (Safety Plus) gemäß DIN VDE 0620-1.
