



Cinch audio insert Breakout cable



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	5633 01	1	01	4010337460343
 pure white glossy	5633 03	1	01	4010337460350
 black matt	5633 10	1	01	4010337460367

Technical data

Installation depth	
- Breakout cable:	mind. 40 mm
Wave impedance for breakout cable:	75 Ω
Length of the breakout cable:	200 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40