




## DVI (24+5) insert Breakout cable



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	5645 01	1	01	4010337460756
 pure white glossy	5645 03	1	01	4010337460763
 black matt	5645 10	1	01	4010337460770

## Technical data

Installation depth	
- Breakout cable:	mind. 58 mm
Length of the breakout cable:	200 mm

## Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40