




USB 3.0 type A insert Gender changer



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 5682 01 | 1 | 01 | 4010337461968 |
|  pure white glossy | 5682 03 | 1 | 01 | 4010337461975 |
|  black matt | 5682 10 | 1 | 01 | 4010337461982 |

Technical data

Installation depth
- Gender changer: mind. 20 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40