

**Interruptor pulsador 10 AX 250 V~ con tecla basculante**  
**Interruptor en cruz**



| Especificación                                                                                            | Ref.     | UE  | SP | EAN           |
|-----------------------------------------------------------------------------------------------------------|----------|-----|----|---------------|
|  blanco crema brillante | 0127 01  | 1/5 | 01 | 4010337127017 |
|  blanco brillante      | 0127 03  | 1/5 | 01 | 4010337127031 |
|  blanco mate           | 0127 27  | 1/5 | 01 | 4010337127277 |
|  antracita             | 0127 28  | 1/5 | 11 | 4010337127284 |
|  color aluminio        | 0127 26  | 1/5 | 11 | 4010337127260 |
|  negro mate            | 0127 005 | 1/5 | 11 | 4010337037989 |
|  gris mate             | 0127 015 | 1/5 | 11 | 4010337077169 |
|  acero inoxidable      | 0127 600 | 1/5 | 11 | 4010337021759 |
|  bronce                | 0127 603 | 1/5 | 11 | 4010337106067 |

## Datos técnicos

|                                                                         |                     |
|-------------------------------------------------------------------------|---------------------|
| Profundidad de instalación:                                             | 28 mm               |
| Sección de conexión<br>- para conductores rígidos y flexibles de hasta: | 2,5 mm <sup>2</sup> |
| Potencia nominal<br>- LEDi/ CFLi:                                       | 100 W               |

---