

Interruptor de control con pulsador 10 AX de 250 V~ con tecla basculante
Interruptor de conmutación universal



Especificación	Ref.	UE	SP	EAN
 blanco crema brillante	0136 01	1/5	01	4010337136019
 blanco brillante	0136 03	1/5	01	4010337136033
 blanco mate	0136 27	1/5	01	4010337136279
 antracita	0136 28	1/5	11	4010337136286
 color aluminio	0136 26	1/5	11	4010337136262
 negro mate	0136 005	1/5	11	4010337037941
 gris mate	0136 015	1/5	11	4010337077190
 acero inoxidable	0136 600	1/5	11	4010337021766
 bronce	0136 603	1/5	11	4010337106081

Datos técnicos

Profundidad de instalación:	28 mm
Sección de conexión - para conductores rígidos y flexibles de hasta:	2,5 mm ²
Potencia nominal - LEDi/ CFLi:	100 W

Notes

- También se puede conectar con iluminación.

En la entrega

- En la entrega se incluye el elemento de lámpara de neón de 230 V~, 1,5 mA.
-