

blanc



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 40	10/100	5,97	01	4010337211402
 2x	0212 40	10		01	4010337212409
 3x	0213 40	10		01	4010337213406
 4x	0214 40	1/5		01	4010337214403
 5x	0215 40	1/5		01	4010337215400

Caractéristiques

- Incassable.

Indications

- Convient également pour installations en goulotte.