

Cadre de finition Gira E2 acier inoxydable



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|---------|-----|----------------|----|---------------|
|  1x | 0211 33 | 10 | 18,54 | 11 | 4010337019794 |
|  2x | 0212 33 | 10 | 28,73 | 11 | 4010337019800 |
|  2x sans nervure centrale | 1002 33 | 10 | 28,73 | 11 | 4010337019848 |
|  3x | 0213 33 | 1/5 | 52,82 | 11 | 4010337019817 |
|  4x | 0214 33 | 1/5 | 81,97 | 11 | 4010337019824 |
|  5x | 0215 33 | 1/5 | 124,83 | 11 | 4010337019831 |

Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.