

Bascule avec symbole Porte



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|---|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 0287 01 | 10 | 5,65 | 01 | 4010337287018 |
|  blanc brillant | 0287 03 | 10 | 5,65 | 01 | 4010337287032 |
|  blanc satiné | 0287 27 | 10 | 5,65 | 01 | 4010337287278 |
|  anthracite | 0287 28 | 1 | 6,14 | 11 | 4010337287285 |
|  teinte alu | 0287 26 | 1 | 9,29 | 11 | 4010337287261 |
|  noir mat | 0287 005 | 1 | 9,29 | 11 | 4010337038283 |
|  gris mat | 0287 015 | 1 | 9,29 | 11 | 4010337079637 |
|  acier inoxydable | 0287 600 | 1 | 16,40 | 11 | 4010337021704 |
|  bronze | 0287 603 | 1 | 16,94 | 11 | 4010337097662 |

