









## Cache avec bouton pour variateur et potentiomètre électronique



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	0650 01	10	6,71	02	4010337650010
 blanc brillant	0650 03	10/100	6,71	02	4010337650034
 blanc satiné	0650 27	10	6,71	02	4010337650270
 anthracite	0650 28	10	10,07	02	4010337650287
 teinte alu	0650 26	10	15,30	02	4010337650263
 noir mat	0650 005	10	15,30	02	4010337036593
 gris mat	0650 015	10	15,30	02	4010337081210
 acier inoxydable	0650 600	1	21,40	02	4010337022329