

Prise avec contact de mise à la terre EURO-US 16 A 250 V~



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2840 01	10		29	4010337840015
 blanc brillant	2840 03	10		29	4010337840039
 blanc satiné	2840 27	10		29	4010337840275
 anthracite	2840 28	10		29	4010337840282
 teinte alu	2840 26	10		29	4010337840268
noir mat	2840 005	10		11	4010337037873
 gris mat	2840 015	1		11	4010337087151
 Acier inoxydable (laqué)	2840 600	10		11	4010337022213

Caractéristiques techniques

Profondeur d'encastrement: 20 mm