

**Pulsante 10 AX 250 V~ con bilanciere diritto con finestra di controllo  
Commutatore a 1 polo**

Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco puro brillante	0120 201	1/5	20,63	11	4010337065982
 bianco puro satinato	0120 27	1/5	20,63	01	4010337029465
 antracite	0120 28	1/5	21,37	11	4010337029489
 color alluminio	0120 26	1/5	24,57	11	4010337029472
 nero opaco	0120 005	1/5	24,57	11	4010337037927
 acciaio inox	0120 600	1/5	31,34	11	4010337021247

**Dati tecnici**

Profondità di montaggio: 28 mm

Sezione dei conduttori  
- per conduttori rigidi e flessibili fino a: 2,5mm<sup>2</sup>**Avvisi**

- Collegabile anche illuminato.