

**Interruttore a pulsante 10 AX 250 V~ con bilanciere 2 moduli
Doppio interruttore**



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|-----|-----------------------|----|---------------|
|  bianco crema brillante | 0125 01 | 1/5 | 28,37 | 01 | 4010337125013 |
|  bianco puro brillante | 0125 03 | 1/5 | 28,37 | 01 | 4010337125037 |
|  bianco puro satinato | 0125 27 | 1/5 | 28,37 | 01 | 4010337125273 |
|  antracite | 0125 28 | 1/5 | 28,88 | 11 | 4010337125280 |
|  color alluminio | 0125 26 | 1/5 | 32,08 | 11 | 4010337125266 |
|  nero opaco | 0125 005 | 1/5 | 32,08 | 11 | 4010337038016 |
|  grigio opaco | 0125 015 | 1/5 | 32,08 | 11 | 4010337077138 |
|  acciaio inox | 0125 600 | 1/5 | 39,15 | 11 | 4010337021780 |
|  bronzo | 0125 603 | 1/5 | 38,65 | 11 | 4010337106012 |

Dati tecnici

Profondità di montaggio

- 0125 ...: 28 mm

- 0128 ...: 32 mm

Sezione dei conduttori

- per conduttori rigidi e flessibili fino a: 2,5mm²

Potenza nominale

- LEDi/CFLi: 100 W