

**Interruttore di controllo a pulsante 10 AX 250 V~ con bilanciere
Deviatore universale**



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0136 01	1/5	34,39	01	4010337136019
 bianco puro brillante	0136 03	1/5	34,39	01	4010337136033
 bianco puro satinato	0136 27	1/5	34,39	01	4010337136279
 antracite	0136 28	1/5	34,92	11	4010337136286
 color alluminio	0136 26	1/5	38,04	11	4010337136262
 nero opaco	0136 005	1/5	38,04	11	4010337037941
 grigio opaco	0136 015	1/5	38,04	11	4010337077190
 acciaio inox	0136 600	1/5	45,16	11	4010337021766
 bronzo	0136 603	1/5	44,07	11	4010337106081

Dati tecnici

Profondità di montaggio: 28 mm

Sezione dei conduttori
- per conduttori rigidi e flessibili fino a: 2,5mm²

Potenza nominale
- LEDi/CFLi: 100 W

Avvisi

- Collegabile anche illuminato.

Contenuto della fornitura

- L'elemento di lampada fluorescente 230 V~ 1,5 mA è in dotazione.
