

Tastschakelaar 10 AX 250 V~ met wip Kruisschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0127 01	1/5	28,29	01	4010337127017
 zuiver wit glanzend	0127 03	1/5	28,29	01	4010337127031
 zuiver wit mat	0127 27	1/5	28,29	01	4010337127277
 antraciet	0127 28	1/5	28,85	11	4010337127284
 kleur aluminium	0127 26	1/5	32,03	11	4010337127260
 zwart mat	0127 005	1/5	32,03	11	4010337037989
 grijs mat	0127 015	1/5	32,03	11	4010337077169
 edelstaal	0127 600	1/5	39,06	11	4010337021759
 brons	0127 603	1/5	38,27	11	4010337106067

Technische gegevens

Inbouwdiepte: 28 mm

Aansluitingdoorsnede
- voor stijve en flexibele geleiders tot: 2.5mm²

Nominaal vermogen
- LEDi/ CFLi: 100 W
