

Wip



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0296 01	10	4,03	21	4010337296010
 zuiver wit glanzend	0296 03	10/100	4,03	21	4010337296034
 zuiver wit mat	0296 27	10/100	4,03	21	4010337296270
 antraciet	0296 28	10/100	4,74	11	4010337296287
 kleur aluminium	0296 26	10	7,93	11	4010337296263
 zwart mat	0296 005	10	7,93	11	4010337038061
 grijs mat	0296 015	10	7,93	11	4010337080220
 edelstaal	0296 600	10	14,96	11	4010337021667
 brons	0296 603	10	15,59	11	4010337097747

Aanwijzingen

- Afdekraam (1- tot 5-voudig) uit de schakelaarprogramma's Standard 55 en Gira E2 in combinatie met de afdichtset ook geschikt voor de installatie van wipchakelaars en wipdrukcontacten spatwaterdicht IP44 (geldt niet voor wip 2-voudig).
