

Tastschakelaar 10 AX 250 V~ met afdekking en wip 2-voudig
Wisselschakelaar 2-voudig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit	0128 40	1/5	55,22	01	4010337128403
 grijs	0128 42	1/5	55,55	11	4010337128427
 rood	0128 43	1/5	55,55	11	4010337128434
 blauw	0128 46	1/5	55,55	11	4010337128465
 zwart	0128 47	1/5	55,55	11	4010337128472

Technische gegevens

Inbouwdiepte	
- 0125 ...:	28 mm
- 0128 ...:	32 mm
Aansluitingdoorsnede	
- voor stijve en flexibele geleiders tot:	2.5mm²
Nominaal vermogen	
- LEDi/ CFLi:	100 W