

Tast-controleschakelaar 10 AX 250 V~ met wip
Universele uit-wisselschakelaar



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0136 01	1/5	43,13	01	4010337136019
 zuiver wit glanzend	0136 03	1/5	43,13	01	4010337136033
 zuiver wit mat	0136 27	1/5	43,13	01	4010337136279
 antraciet	0136 28	1/5	43,89	11	4010337136286
 kleur aluminium	0136 26	1/5	47,78	11	4010337136262
 zwart mat	0136 005	1/5	47,78	11	4010337037941
 grijs mat	0136 015	1/5	47,78	11	4010337077190
 edelstaal	0136 600	1/5	56,62	11	4010337021766
 brons	0136 603	1/5	61,19	11	4010337106081

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm ²
Nominaal vermogen - LEDi/ CFLi:	100 W

Aanwijzingen

- Ook verlichtbaar aan te sluiten.

Levering

- Glimlampelement 230 V~, 1,5 mA is bij de levering inbegrepen.
-