







## Dekkramme Gira E3 grå soft-touch med bæreramme renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 412 1403515	10	11	4010337023890
 Dobbel	0212 412 1403532	10	11	4010337023906
 dobbel, uten mellomstykke	1002 412 1403549	10	11	4010337023944
 3-dobbel	0213 412 1403566	1/5	11	4010337023913
 4-dobbel	0214 412 1403583	1	11	4010337023920
 5-dobbel	0215 412 1479282	1/5	11	4010337023937

### Egenskaper

- Bruddsikker.

### Merknader

- Soft-touch-overflate.  
- NCS-verdi: lign. NCS S 3500-N