

**Tryck-kontrollbrytare 10 AX 250 V~ med vipa
Universal-av-trapp**



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0136 01	1/5	01	4010337136019
 kritvit blank	0136 03	1/5	01	4010337136033
 kritvit sidenmatt	0136 27	1/5	01	4010337136279
 antracit	0136 28	1/5	11	4010337136286
 alufärg	0136 26	1/5	11	4010337136262
 svart matt	0136 005	1/5	11	4010337037941
 grå matt	0136 015	1/5	11	4010337077190
 rostfritt stål	0136 600	1/5	11	4010337021766
 brons	0136 603	1/5	11	4010337106081

Tekniska data

Inbyggnadsdjup:	28 mm
Anslutningsarea	
- För styva och flexibla ledare upp till:	2,5 mm ²
Nominell effekt	
- LEDi/ CFLi:	100 W

Hänvisningar

- Kan även anslutas med belysning.

Leveransen innehåller

- Glimlampselement 230 V~, 1,5 mA ingår i leveransen.
-