

## Vippbrytare British Standard (BS EN 60669-1) 3-delad med vippknappar Universal-av-trapp



| Specifikation                                                                                                 | Artikelnr.          | FE | PS | EAN           |
|---------------------------------------------------------------------------------------------------------------|---------------------|----|----|---------------|
|  cremevit blank             | 2832 01             | 10 | 29 | 4010337832010 |
|  kritvit blank             | 2832 03<br>1850000  | 10 | 29 | 4010337832034 |
|  antracit                  | 2832 28<br>1850002  | 10 | 29 | 4010337832287 |
|  alufärg                   | 2832 26<br>1850001  | 10 | 29 | 4010337832263 |
|  svart matt                | 2832 005            | 10 | 11 | 4010337038528 |
|  grå matt                  | 2832 015<br>1850414 | 10 | 11 | 4010337087120 |
|  Rostfritt stål (lackerat) | 2832 600            | 10 | 29 | 4010337022053 |

### Egenskaper

- Med skruvklämmor.

## Tekniska data

|                                       |                            |
|---------------------------------------|----------------------------|
| Inbyggnadsdjup:                       | 25 mm                      |
| Anslutningsarea<br>- för ledare till: | 2,5 mm <sup>2</sup>        |
| Nominell effekt:                      | 100 W LED-last (IEC 60669) |

---

## Hänvisningar

- Endast för skruvfastsättning.

---