


**Tast-Kontrollschalter 10 AX 250 V~ mit Wippe
Universal-Aus-Wechselschalter**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	0136 01	1/5	34,39	01	4010337136019
 Reinweiß glänzend	0136 03	1/5	34,39	01	4010337136033
 Reinweiß seidenmatt	0136 27	1/5	34,39	01	4010337136279
 Anthrazit	0136 28	1/5	34,92	11	4010337136286
 Farbe Alu	0136 26	1/5	38,04	11	4010337136262
 Schwarz matt	0136 005	1/5	38,04	11	4010337037941
 Grau matt	0136 015	1/5	38,04	11	4010337077190
 Edelstahl	0136 600	1/5	45,16	11	4010337021766
 Bronze	0136 603	1/5	44,07	11	4010337106081

Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm ²
Nennleistung - LEDi/ CFLi:	100 W

Hinweise

- Auch beleuchtbar anzuschließen.

Lieferumfang

- Glimmlampenelement 230 V~, 1,5 mA ist im Lieferumfang enthalten.
