







**Taster 10 A 250 V~ mit gerade stehender Wippe mit Kontrollfenster
Wechsler 1-polig**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß glänzend	0120 201	1/5	20,63	11	4010337065982
 Reinweiß seidenmatt	0120 27	1/5	20,63	01	4010337029465
 Anthrazit	0120 28	1/5	21,37	11	4010337029489
 Farbe Alu	0120 26	1/5	24,57	11	4010337029472
 Schwarz matt	0120 005	1/5	24,57	11	4010337037927
 Edelstahl	0120 600	1/5	31,34	11	4010337021247

Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm ²

Hinweise

- Auch beleuchtbar anzuschließen.

- Lieferfähigkeit vorausgesetzt.
