

Tastschalter 10 AX 250 V~ mit gerade stehender Wippe Universal-Aus-Wechselschalter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß glänzend	0121 201	1/5	17,70	01	4010337052692
 Reinweiß seidenmatt	0121 27	1/5	17,70	01	4010337029311
 Anthrazit	0121 28	1/5	18,20	11	4010337029335
 Farbe Alu	0121 26	1	21,40	11	4010337029328
 Schwarz matt	0121 005	1	21,40	11	4010337037972
 Grau matt	0121 015	1	21,40	11	4010337077091
 Edelstahl	0121 600	1/5	28,42	11	4010337021261

Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm ²
Nennleistung - LEDi/ CFLi:	100 W

Hinweise

- Lieferfähigkeit vorausgesetzt.
