









**Tastschalter 10 AX 250 V~ mit Wippe 2fach  
Wechselschalter 2fach**



| Spezifikation   | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|-----|--------------------|----|---------------|
|  Cremeweiß glänzend   | 0128 01     | 1/5 | 40,02              | 01 | 4010337128014 |
|  Reinweiß glänzend   | 0128 03     | 1/5 | 40,02              | 01 | 4010337128038 |
|  Reinweiß seidenmatt | 0128 27     | 1/5 | 40,02              | 01 | 4010337128274 |
|  Anthrazit           | 0128 28     | 1/5 | 40,54              | 11 | 4010337128281 |
|  Farbe Alu           | 0128 26     | 1/5 | 43,74              | 11 | 4010337128267 |
|  Schwarz matt        | 0128 005    | 1/5 | 43,74              | 11 | 4010337038030 |
|  Grau matt           | 0128 015    | 1/5 | 43,74              | 11 | 4010337077176 |
|  Edelstahl           | 0128 600    | 1/5 | 50,74              | 11 | 4010337021797 |

**Technische Daten**

Einbautiefe  
- 0125 ...: 28 mm

|   |                     |
|---|---------------------|
| - 0128 ...:   | 32 mm               |
| Anschlussquerschnitt<br>- für starre und flexible Leiter bis: | 2,5 mm <sup>2</sup> |
| Nennleistung<br>- LEDi/ CFLi:                                 | 100 W               |

---

## Hinweise

- Lieferfähigkeit vorausgesetzt.

---