

## SCHUKO-Steckdose 16 A 250 V~ mit Shutter



| Spezifikation                                                                               | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---------------------------------------------------------------------------------------------|-------------|-----|--------------------|----|---------------|
|  Reinweiß  | 0453 40     | 1/5 | 15,62              | 01 | 4010337453406 |
|  Grau    | 0453 42     | 1/5 | 15,62              | 11 | 4010337453420 |
|  Rot     | 0453 43     | 1/5 | 15,62              | 11 | 4010337453437 |
|  Grün    | 0453 45     | 1   | 15,62              | 11 | 4010337453451 |
|  Blau    | 0453 46     | 1/5 | 15,62              | 11 | 4010337453468 |
|  Schwarz | 0453 47     | 1/5 | 15,62              | 11 | 4010337453475 |

### Technische Daten

|                                           |                     |
|-------------------------------------------|---------------------|
| Einbautiefe:                              | 31 mm               |
| Anschlussquerschnitt<br>- für Leiter von: | 1,5 mm² bis 2,5 mm² |
| Umgebungstemperatur<br>- Shutter:         | 0 °C bis 45 °C      |

## Hinweise

- Erhöhter Berührungsschutz (Safety Plus) gemäß DIN VDE 0620-1.

---