

## SCHUKO-Steckdose 16 A 250 V~ mit Klappdeckel



| Spezifikation                                                                               | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---------------------------------------------------------------------------------------------|-------------|-----|--------------------|----|---------------|
|  Reinweiß  | 0454 40     | 1/5 | 20,60              | 01 | 4010337454403 |
|  Grau    | 0454 42     | 1/5 | 20,60              | 11 | 4010337454427 |
|  Rot     | 0454 43     | 1/5 | 20,60              | 11 | 4010337454434 |
|  Grün    | 0454 45     | 1   | 20,60              | 11 | 4010337454458 |
|  Blau    | 0454 46     | 1/5 | 20,60              | 11 | 4010337454465 |
|  Schwarz | 0454 47     | 1/5 | 20,60              | 11 | 4010337454472 |

### Technische Daten

|                                           |                     |
|-------------------------------------------|---------------------|
| Einbautiefe:                              | 31 mm               |
| Anschlussquerschnitt<br>- für Leiter von: | 1,5 mm² bis 2,5 mm² |