









Stetigregler mit Tasterschnittstelle 4fach für KNX



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|----|--------------------|----|---------------|
|  Cremeweiß glänzend | 2100 01 | 1 | 353,15 | 06 | 4010337048022 |
|  Reinweiß glänzend | 2100 03 | 1 | 353,15 | 06 | 4010337048039 |
|  Reinweiß seidenmatt | 2100 27 | 1 | 353,15 | 06 | 4010337048060 |
|  Anthrazit | 2100 28 | 1 | 355,79 | 06 | 4010337048077 |
|  Farbe Alu | 2100 26 | 1 | 360,07 | 06 | 4010337048053 |
|  Schwarz matt | 2100 005 | 1 | 360,07 | 06 | 4010337037255 |
|  Grau matt | 2100 015 | 1 | 360,07 | 06 | 4010337083016 |
|  Edelstahl | 2100 600 | 1 | 367,60 | 06 | 4010337021520 |

Merkmale

- Mit dem Stellrad wird der Temperatursollwert verschoben.
 - Ein Präsenztaster dient zur Umschaltung zwischen Komfort- und Stand-by-Betrieb.
 - Die aktuellen Zustände werden am Stetigregler durch LEDs angezeigt.
-

Technische Daten

Einbautiefe: 23 mm
