








Steckdose British Standard (BS 1363) 13 A 250 V~ mit Shutter System 55



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|--|-------------|----|--------------------|----|---------------|
|  Cremeweiß glänzend | 2776 01 | 10 | 18,05 | 29 | 4010337079347 |
|  Reinweiß glänzend | 2776 03 | 10 | 18,05 | 29 | 4010337079354 |
|  Anthrazit | 2776 28 | 10 | 20,67 | 29 | 4010337079378 |
|  Farbe Alu | 2776 26 | 10 | 24,71 | 29 | 4010337079361 |
|  Schwarz matt | 2776 005 | 10 | 24,71 | 29 | 4010337037774 |
|  Grau matt | 2776 015 | 10 | 24,71 | 29 | 4010337086352 |
|  Edelstahl (lackiert) | 2776 600 | 10 | 28,40 | 29 | 4010337022077 |

Merkmale

- Mit Schraubklemmen.

Technische Daten

Einbautiefe: 17 mm

Hinweise

- Nur für Schraubbefestigung.
 - Weitere Funktionen und Varianten auch für die 80er BS-Dose auf Anfrage erhältlich.
-