








**Wipp-Kontrollschalter British Standard (BS EN 60669-1) 20 AX 250 V~mit Wippe
Ausschalter 2-polig**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2834 01	10	45,20	29	4010337078814
 Reinweiß glänzend	2834 03	10	45,20	29	4010337078821
 Anthrazit	2834 28	10	45,69	29	4010337078845
 Farbe Alu	2834 26	10	48,69	29	4010337078838
 Schwarz matt	2834 005	10	48,69	29	4010337038573
 Grau matt	2834 015	10	48,69	29	4010337087137
 Edelstahl	2834 600	10	55,61	29	4010337022305

Merkmale

- Mit Schraubklemmen.

Technische Daten

Einbautiefe:	24 mm
Anschlussquerschnitt - für Leiter bis:	2 x 4 mm ² oder 1 x 6 mm ²

Hinweise

- Nur für Schraubbefestigung.
 - BS EN 60669-1.
-