

Wippschalter British Standard (BS EN 60669-1) 20 AX 250 V~ mit Wippe Ausschalter 2-polig



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|----|--------------------|----|---------------|
|  Cremeweiß glänzend | 2836 01 | 10 | 37,56 | 29 | 4010337078944 |
|  Reinweiß glänzend | 2836 03 | 10 | 37,56 | 29 | 4010337078951 |
|  Anthrazit | 2836 28 | 10 | 38,26 | 29 | 4010337078975 |
|  Farbe Alu | 2836 26 | 1 | 41,30 | 29 | 4010337078968 |
|  Schwarz matt | 2836 005 | 10 | 41,30 | 29 | 4010337038566 |
|  Grau matt | 2836 015 | 10 | 41,30 | 29 | 4010337087144 |
|  Edelstahl | 2836 600 | 10 | 47,99 | 29 | 4010337021933 |

Merkmale

- Mit Schraubklemmen.

Technische Daten

| | |
|---|---|
| Einbautiefe: | 24 mm |
| Anschlussquerschnitt - für Leiter bis: | 2 x 4 mm ² oder 1 x 6 mm ² |

Hinweise

- Nur für Schraubbefestigung.
 - BS EN 60669-1.
-