








**Wippschalter British Standard (BS EN 60669-1) 20 AX 250 V~ mit Wippe
Ausschalter 2-polig**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2836 01	10	36,40	29	4010337078944
 Reinweiß glänzend	2836 03	10	36,40	29	4010337078951
 Anthrazit	2836 28	10	37,07	29	4010337078975
 Farbe Alu	2836 26	1	40,02	29	4010337078968
 Schwarz matt	2836 005	10	40,02	29	4010337038566
 Grau matt	2836 015	10	40,02	29	4010337087144
 Edelstahl	2836 600	10	46,50	29	4010337021933

Merkmale

- Mit Schraubklemmen.

Technische Daten

Einbautiefe:	24 mm
Anschlussquerschnitt - für Leiter bis:	2 x 4 mm ² oder 1 x 6 mm ²

Hinweise

- Nur für Schraubbefestigung.
 - BS EN 60669-1.
-