

## SCHUKO-Steckdose 16 A 250 V~ mit Aufdruck "EDV" System 55



| Spezifikation   | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|-----|--------------------|----|---------------|
|  Cremeweiß glänzend   | 4458 01     | 1/5 | 8,71               | 01 | 4010337093176 |
|  Reinweiß glänzend   | 4458 03     | 1/5 | 8,71               | 01 | 4010337093190 |
|  Reinweiß seidenmatt | 4458 27     | 1/5 | 8,71               | 01 | 4010337093213 |
|  Anthrazit           | 4458 28     | 1/5 | 9,97               | 11 | 4010337093220 |
|  Farbe Alu           | 4458 26     | 1/5 | 14,49              | 11 | 4010337093206 |
|  Schwarz matt        | 4458 005    | 1/5 | 14,49              | 11 | 4010337093169 |
|  Grau matt           | 4458 015    | 1/5 | 14,49              | 11 | 4010337093183 |

### Merkmale

- Geerdeter Tragring.

## Technische Daten

|   |   |
|---|---|
| Einbautiefe:                              | 32 mm                                       |
| Leitergut:                                | starr und flexibel                          |
| Anschlussquerschnitt<br>- für Leiter von: | 1,5 mm <sup>2</sup> bis 2,5 mm <sup>2</sup> |

---

## Hinweise

- Mit erhöhtem Anpressdruck des Erdungsbügels geprüft nach T.N.O.

---