









SCHUKO-Steckdose 16 A 250 V~ ohne Befestigungskrallen System 55



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|--------|--------------------|----|---------------|
|  Cremeweiß glänzend | 4466 01 | 10 | 6,90 | 21 | 4010337095088 |
|  Reinweiß glänzend | 4466 03 | 10 | 6,90 | 21 | 4010337095101 |
|  Reinweiß seidenmatt | 4466 27 | 10/100 | 6,90 | 21 | 4010337095125 |
|  Anthrazit | 4466 28 | 10/100 | 8,59 | 11 | 4010337095132 |
|  Farbe Alu | 4466 26 | 10 | 13,10 | 11 | 4010337095118 |
|  Schwarz matt | 4466 005 | 10/100 | 13,10 | 11 | 4010337095071 |
|  Grau matt | 4466 015 | 1/5 | 13,10 | 11 | 4010337095095 |
|  Edelstahl | 4466 600 | 10 | 21,23 | 11 | 4010337095149 |

Merkmale

- Vereinfachte Installation durch patentierte Anordnung der großen Schlüssellochprofile mittels Dosenschrauben.
- Geringe Einbautiefe.
- Große, ergonomisch geformte Lösehebel.
- Stabiler Erdungsbügel mit massiven Erdungsfingern.
- Stabiler und korrosionsbeständiger Stahltragring.
- Bruchsicherer Thermoplastsockel.

Technische Daten

| | |
|---|---|
| Einbautiefe: | 32 mm |
| Leitergut: | starr und flexibel |
| Anschlussquerschnitt - für Leiter von: | 1,5 mm ² bis 2,5 mm ² |
