









System 3000 Bedieneinsatz 2fach



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  Cremeweiß glänzend | 5362 01 | 1/5 | 42,26 | 02 | 4010337063841 |
|  Reinweiß glänzend | 5362 03 | 1/5 | 42,26 | 02 | 4010337063858 |
|  Reinweiß seidenmatt | 5362 27 | 1/5 | 42,26 | 02 | 4010337063896 |
|  Anthrazit | 5362 28 | 1/5 | 45,14 | 02 | 4010337063902 |
|  Farbe Alu | 5362 26 | 1 | 49,71 | 02 | 4010337063889 |
|  Schwarz matt | 5362 005 | 1/5 | 49,71 | 02 | 4010337063919 |
|  Grau matt | 5362 015 | 1/5 | 49,71 | 02 | 4010337087229 |
|  Edelstahl | 5362 600 | 1 | 57,97 | 02 | 4010337063926 |

Technische Daten

Umgebungstemperatur: -20 °C bis +45 °C