








Tastschalter 10 AX 250 V~ mit gerade stehender Wippe Kreuzschalter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß glänzend	0123 201	1/5	28,29	01	4010337052708
 Reinweiß seidenmatt	0123 27	1/5	28,29	01	4010337029342
 Anthrazit	0123 28	1/5	28,85	11	4010337029366
 Farbe Alu	0123 26	1	32,03	11	4010337029359
 Schwarz matt	0123 005	1	32,03	11	4010337037996
 Grau matt	0123 015	1	32,03	11	4010337077114
 Edelstahl	0123 600	1	39,06	11	4010337021254

Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm ²
Nennleistung - LEDi/ CFLi:	100 W

Hinweise

- Lieferfähigkeit vorausgesetzt.
