

**Tastschalter 10 AX 250 V~ mit Abdeckung und Wippe  
Universal-Aus-Wechselschalter**

| Spezifikation                                                                               | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---------------------------------------------------------------------------------------------|-------------|-----|--------------------|----|---------------|
|  Reinweiß | 0126 40     | 1/5 | 21,41              | 01 | 4010337126409 |
|  Grau    | 0126 42     | 1/5 | 21,41              | 11 | 4010337126423 |
|  Rot     | 0126 43     | 1/5 | 21,41              | 11 | 4010337126430 |
|  Blau    | 0126 46     | 1/5 | 21,41              | 11 | 4010337126461 |
|  Schwarz | 0126 47     | 1/5 | 21,41              | 11 | 4010337126478 |

**Technische Daten**

|                                                               |         |
|---------------------------------------------------------------|---------|
| Einbautiefe:                                                  | 28 mm   |
| Anschlussquerschnitt<br>- für starre und flexible Leiter bis: | 2,5 mm² |
| Nennleistung<br>- LEDi/ CFLi:                                 | 100 W   |

**Hinweise**

- Soll dieser Schalter beleuchtet werden, bitte Kontrollschalter vorsehen.