

SCHUKO-Steckdose 16 A 250 V~ mit Kontrolllicht



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0182 40	1/5	28,01	01	4010337182405
 Grau	0182 42	1/5	28,01	11	4010337182429
 Rot	0182 43	1/5	28,01	11	4010337182436
 Grün	0182 45	1	28,01	11	4010337182450
 Blau	0182 46	1/5	28,01	11	4010337182467
 Schwarz	0182 47	1/5	28,01	11	4010337182474

Merkmale

- Mit Schraubklemmen.

Technische Daten

Einbautiefe:	31 mm
Anschlussquerschnitt - für Leiter von:	1,5 mm² bis 2,5 mm²