

SCHUKO-Steckdose 16 A 250 V~



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0188 40	10/100	13,20	01	4010337188407
 Grau	0188 42	1/5	13,20	11	4010337188421
 Rot	0188 43	1/5	13,20	11	4010337188438
 Grün	0188 45	1/5	13,20	11	4010337188452
 Blau	0188 46	1/5	13,20	11	4010337188469
 Schwarz	0188 47	1/5	13,20	11	4010337188476

Technische Daten

Einbautiefe:	31 mm
Anschlussquerschnitt - für Leiter von:	1,5 mm² bis 2,5 mm²