








## Abdeckrahmen Gira Standard 55 Reinweiß seidenmatt



| Spezifikation   | Bestell-Nr. | VE     | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|--------|--------------------|----|---------------|
|  1fach                  | 0211 04     | 10/100 | 2,99               | 21 | 4010337211044 |
|  1,5fach               | 1001 04     | 10     | 4,04               | 01 | 4010337881315 |
|  2fach                 | 0212 04     | 10/100 | 5,12               | 21 | 4010337212041 |
|  2fach ohne Mittelsteg | 1002 04     | 10     | 3,78               | 01 | 4010337002048 |
|  3fach                 | 0213 04     | 10/100 | 9,02               | 01 | 4010337213048 |
|  4fach                 | 0214 04     | 1/5    | 15,60              | 01 | 4010337214045 |
|  5fach                 | 0215 04     | 1/5    | 25,66              | 01 | 4010337215042 |

### Merkmale

- Bruchsicher.

## Hinweise

- Auch für Kanalinstallationen geeignet.
  - Abdeckrahmen (1- bis 5fach) in Verbindung mit Dichtungsset auch für die Montage wassergeschützt Unterputz IP44 geeignet.
-