








## Wippschalter 3fach 10 AX 250 V~ mit Wippen Universal-Aus-Wechselschalter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2832 01	10	35,18	29	4010337832010
 Reinweiß glänzend	2832 03	10	35,18	29	4010337832034
 Anthrazit	2832 28	10	37,81	29	4010337832287
 Farbe Alu	2832 26	10	41,83	29	4010337832263
 Schwarz matt	2832 005	10	41,83	11	4010337038528
 Grau matt	2832 015	10	41,83	11	4010337087120
 Edelstahl (lackiert)	2832 600	10	45,56	29	4010337022053

### Merkmale

- Mit Schraubklemmen.

## Technische Daten

Einbautiefe:	25 mm
Anschlussquerschnitt - für Leiter bis:	2,5 mm <sup>2</sup>

---

## Hinweise

- Nur für Schraubbefestigung.
-