








## Wippschalter 3fach 10 AX 250 V~ mit Wippen Universal-Aus-Wechselschalter



| Spezifikation  | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN           |
|--|-------------|----|--------------------|----|---------------|
|  Cremeweiß glänzend    | 2832 01     | 10 | 34,09              | 29 | 4010337832010 |
|  Reinweiß glänzend    | 2832 03     | 10 | 34,09              | 29 | 4010337832034 |
|  Anthrazit            | 2832 28     | 10 | 36,64              | 29 | 4010337832287 |
|  Farbe Alu            | 2832 26     | 10 | 40,53              | 29 | 4010337832263 |
|  Schwarz matt         | 2832 005    | 10 | 40,53              | 11 | 4010337038528 |
|  Grau matt            | 2832 015    | 10 | 40,53              | 11 | 4010337087120 |
|  Edelstahl (lackiert) | 2832 600    | 10 | 44,15              | 29 | 4010337022053 |

### Merkmale

- Mit Schraubklemmen.

## Technische Daten

|   |                     |
|---|---------------------|
| Einbautiefe:                              | 25 mm               |
| Anschlussquerschnitt<br>- für Leiter bis: | 2,5 mm <sup>2</sup> |

---

## Hinweise

- Nur für Schraubbefestigung.

---