








## Tastschalter 10 AX 250 V~ mit gerade stehender Wippe 2fach Serienschalter



| Spezifikation   | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|-----|--------------------|----|---------------|
|  Reinweiß glänzend    | 2860 201    | 1/5 | 28,37              | 01 | 4010337065876 |
|  Reinweiß seidenmatt | 2860 27     | 1/5 | 28,37              | 01 | 4010337029373 |
|  Anthrazit           | 2860 28     | 1/5 | 28,88              | 11 | 4010337029397 |
|  Farbe Alu           | 2860 26     | 1/5 | 32,08              | 11 | 4010337029380 |
|  Schwarz matt        | 2860 005    | 1/5 | 32,08              | 11 | 4010337038023 |
|  Grau matt           | 2860 015    | 1/5 | 32,08              | 11 | 4010337087199 |
|  Edelstahl           | 2860 600    | 1/5 | 39,15              | 11 | 4010337021223 |

### Technische Daten

|                                       |                     |
|---------------------------------------|---------------------|
| Einbautiefe                           |                     |
| - 2860 ...                            | 28 mm               |
| - 2861 ...                            | 32 mm               |
| Anschlussquerschnitt                  |                     |
| - für starre und flexible Leiter bis: | 2,5 mm <sup>2</sup> |
| Nennleistung                          |                     |
| - LEDi/ CFLi:                         | 100 W               |

Abbildungen sind ähnlich und können vom Original abweichen.  
Preise gültig für Schweiz mit Preisstand 02/24.

---

## Hinweise

- Lieferfähigkeit vorausgesetzt.

---